## **Cohesive Slot Sampler**

Composite sampling of Cohesive powders

The Cohesive Slot Sampler has been specially adapted from the popular Slot Sampler (on pages 70-71). Scrapers have been added to push the non flowing powder into the sample slots.

Scrapers are fully welded to give a hygienic, GMP correct sampler.

- Multilevel (composite samples)
- 316L Stainless steel construction
- Suitable for sticky, cohesive powders







## **QUICK QUOTE**

					Let incate
Part No.	Sampler Length	Number of Sam- pling Slots	Maximum Sample Volume	Diameter*	Material
675 2210A600	600mm	3	110ml	25mm	316L ss
675 2210A1000	1000mm	4	190ml	25mm	316L ss
675 2210A1500	1500mm	5	300ml	25mm	316L ss

\* Diameter does not include scrapers. Scrapers are approximately 10mm high