

Mini Corer

- Suitable for sampling wax, cheese, greases, powders, granules
- Made from 316 stainless steel
- High quality bright polish finish
- Crevice free construction

Operation:

1. Rotate the handle as the sampler is pushed into the product. A core of the product will be cut.
2. Remove sampler.



Stock No.	Description	Length	Maximum Diameter
675 7008A01	MiniCorer	190mm	18mm
675 8505A12	Storage Case		

QUOTE REQUEST 

BUY ONLINE 

Corer

- Suitable for sampling wax, cheese, greases, powders, granules
- Made from 316 stainless steel
- High quality bright polish finish
- Crevice free construction

Operation:

1. Push the Outer tube into the product.
2. Use the Push Rod to eject the core of product from the Outer Tube



Stock No.	Description	Length	Maximum Diameter
675 7009A01	Corer	230mm	12mm
675 8505A12	Storage Case		

QUOTE REQUEST 

BUY ONLINE 

Maxi Corer

- 316 stainless steel construction
- Two sizes
- Crevice free
- Satin finish



Stock No.	Diameter	Length	Blade Length
675 7010A01	25mm	300mm	200mm
675 7010A02	25mm	600mm	500mm

QUOTE REQUEST 

BUY ONLINE 