

## UniPump Sampler with hose



UniPump Sampler with PVC hose and hose weight made of stainless steel. For deep, hard-to-reach places. The mass of the metal tube drags the hose to any depth.

- Suction hose PVC, 2.50 m long
- Complete in a handy transport case incl. sample bottle PP 1000 ml, vacuum pump, universal bottle adapter, hose weight made of AISI 304 (1.4301), 20 seal-it bottle seals
- Universal bottle adapter made of PVC, for bottle necks Ø 24 mm, 32 mm, 39 mm and 50 mm nominal dimension, for sample bottles 100–1000 ml

## Use

- 1. Lower the suction hose to the required depth.
- 2. Attach the adapter to the sampling bottle.
- 3. Create a vacuum using the handpump and collect the sample.
- 4. Remove the filled sample bottle, close and label it.

UniPump Sampler with hose	
	Item no.
	711 53142000
Accessories	
Description	Item no.
Suction hose for replacement PVC, 2,5 m	711 53142002
Sampling bottle PP, 100 ml	711 03190100
s II I will po oco I	E11 021002F0
Sampling bottle PP, 250 ml	711 03190250
Sampling bottle PP, 250 ml Sampling bottle PP, 500 ml	711 03190250

## UniPumpSampler "Ex"




Sampler especially developed for sampling flammable liquids of Hazard Category AI (VbF, e.g. fuel). Glass bottle and hose are connected in such a way that they conduct electricity and are earthed via an earthing cable.

- ▶ Complete in a handy transport case incl. 4 m hose (NBR), glass bottle 1000 ml, bottle adapter, bottle stand, vacuum pump, earthing cable and hose-weight made of brass
- PTB approval D-333-009 618/00

## Use

- 1. Earth the device.
- 2. Lower the suction hose to the required depth.
- 3. Attach the adapter to the sampling bottle.
- 4. Create a vacuum using the handpump and collect the sample.
- 5. Remove the filled sample bottle, close and label it.



UniPump Sampler "Ex"			Ex
		Item no.	
	711	53143000	
<b>G</b> Accessories			
Description		Item no.	
Glass sampling bottle 1000 ml, GL 45	711	53140100	

