

Stainless Dipper

GMP Correct Liquid Sampler

- 316 stainless steel construction
- Fully welded
- Satin finish

Stock No.	Nominal Volume	Length	Cup Diameter
675 5005A100	100ml	600mm	39mm
675 5005B100	100ml	1000mm	39mm
675 5005A250	250ml	600mm	64mm
675 5005B250	250ml	1000mm	64mm
675 5005A500	500ml	600mm	90mm
675 5005B500	500ml	1000mm	90mm




[QUICK QUOTE LINK](#) [ONLINE PRICING LINK](#)

PTFE Dipper

Excellent Chemical Resistance - GMP correct

- PTFE product contact parts
- Screw-in extension rods to increase the length of the handle



Stock No.	Nominal Volume	Cup Diameter	Handle
675 5100A100	100ml	55mm	600mm long - removable
675 5100A250	250ml	70mm	600mm long - removable
675 5100A500	500ml	80mm	600mm long - removable
675 5100A1000	1000ml	105mm	600mm long - removable
675 5100E600	Handle Extension rod - 600mm long		

[QUICK QUOTE LINK](#)

[ONLINE PRICING LINK](#)



Chemical Dipper

Robust Polypropylene Dipper

- Ideal for general industrial applications
- Durable polypropylene construction

Part No.	Beaker Volume	Overall Length
675 5065F250	250ml	1000mm
675 5065F500	500ml	1000mm
675 5065F1000	1000ml	1000mm

[QUICK QUOTE LINK](#)

[ONLINE PRICING LINK](#)



Utility Dipper


Simple Liquid Sampler

An all stainless steel sampler suitable for sampling liquids and suspensions.

- Takes a sample at the surface of the liquid
- Made from 304 Stainless steel

Operation

1. Insert the sampler into the product. The liquid will flow into the sampler.
2. Withdraw the sampler from the product
3. Raise the centre control rod to discharge the sample



Raise the centre control rod (shown in red) to discharge the product



Stock No.	Length	Volume	Cup Diameter
675 5170A50	460mm	50ml	32mm
675 5170A100	540mm	100ml	32mm

[QUICK QUOTE LINK](#)

[ONLINE PRICING LINK](#)

Multi Dipper 2


Multilevel Liquid Sampler

The Multi Dipper 2 is the ideal solution for taking liquid samples from different levels. The sample collection bottles remain closed until the operator uses the control chain to remove the stoppers.

High security stainless steel shackles are used to secure the plugs to the control chain

Product contact parts are:

- Sampler frame 316ss
- Control Chain 316ss
- Plugs 316ss
- Plug Shackles 316ss
- Sample Bottle HDPE



Operation

1. Screw the bottle into the holders
2. Insert the plugs into the tops of the sample bottles
3. Connect the Control Chain to the plugs
4. Insert the assembled sampler into the liquid to be sampled
5. Pull on the Control Chain to open the bottles
6. Remove from the liquid tank

Special sizes and designs are available on request

Stock No.	Length	Bottles
675 5045A1000	1000mm	3 x 250ml included (675 8165A250)
675 5045A1500	1500mm	3 x 250ml included (675 8165A250)
675 5045A2000	2000mm	3 x 250ml included (675 8165A250)
675 8165A250	Spare sample bottle - HDPE - 250ml	

[QUICK QUOTE LINK](#)

[ONLINE PRICING LINK](#)



Enviro Dipper

The Enviro Dipper is a simple and yet effective method of taking a surface sample. Simply lower the bucket into the liquid.

The stainless steel bucket can be ordered with either a stainless steel chain or a braided polypropylene cord.

STOCK NO	DESCRIPTION
675 A724300	Stainless Steel Bucket - 300ml - 304ss
675 5070S10	Chain - 316 stainless steel - 10m - with 316ss shackle
675 5070S25	Chain - 316 stainless steel - 25m - with 316ss shackle
675 5070S50	Chain - 316 stainless steel - 50m - with 316ss shackle
675 5070P10	Braided Cord - Polypropylene 10m
675 5070P25	Braided Cord - Polypropylene 25m
675 5070P50	Braided Cord - Polypropylene 50m
675 5070D04	Standard heavy duty hand reel

[QUICK QUOTE LINK](#)

[ONLINE PRICING LINK](#)



PTFE Mini Dipper

Excellent Chemical Resistance - GMP correct

Ideal for surface sampling small volumes of liquids

- PTFE construction
- Chemically resistant



Stock No.	Volume	Diameter	Handle
675 5100A10	10mm	25mm	155mm long - fixed in place

[QUICK QUOTE LINK](#)

[ONLINE PRICING LINK](#)

Disposable Ladle

Efficient surface sampling of liquids



Stock No.	Volume	Diameter	Pre-Sterilized	Material	Per Box
675 8053H50	50 ml	48 mm	No	HDPE	40
675 8053H50S	50 ml	48 mm	Yes	HDPE	40

[QUICK QUOTE LINK](#)

[ONLINE PRICING LINK](#)

Stainless Ladle

- Satin finish
- 304 or 316 stainless steel
- All stainless steel construction
- Crevice free construction



Stock No.	Stainless Steel	Bowl Volume	Bowl Diameter	Handle Length
675 A326150	316	150ml	88mm	370mm
675 A32450	304	50ml	63mm	275mm
675 A324120	304	120ml	82mm	345mm
675 A324150	304	150ml	92mm	350mm
675 A324200	304	200ml	100mm	365mm

[QUICK QUOTE LINK](#)

[ONLINE PRICING LINK](#)