

Pocket Sampler (Individual Pockets)


Multilevel Sampler for taking discrete samples

The Pocket Sampler is used in thousands of pharmaceutical and industrial manufacturing facilities all over the world. The Pocket Sampler is ideal for taking discrete samples from free flowing powders and granules. The sampler is available in a range of sizes and designs.

Its robust stainless steel design means it will give years of service.

Operation

1. Insert the sampler into the product
2. At the required depth rotate handle to expose the collecting pockets, the product will flow into the collecting pockets
3. Rotate handle to close pockets and remove sampler
4. See below for details on how to empty the sampler



Pocket Sampler Holder

- Enables the samples to be deposited directly into collecting bottles
- All stainless steel construction
- Supplied complete with stainless steel funnels



Bayonet Handle

- Allows simple operation
- Quick disconnect system so sampler can be dismantled in seconds.
- Robust design

(Bayonet handle is available on the 1220A and 1220B models)



QUOTE REQUEST ✓

Sealing Sleeves

- Enables one pocket to be emptied at a time Simply clip on to cover
- Easy to remove



Tips

- Samplers are supplied with pointed tips as standard
- Rounded tips are available as an option



BUY ONLINE ✓

Stock No.	Outer Tube	Inner Rod	Outer Diameter	No. Pockets	Volume Per Pocket	Length
675 1220A600	316L stainless	PTFE	25mm	3	15ml	600mm
675 1220A900	316L stainless	PTFE	25mm	3	20ml	900mm
675 1220A1500	316L stainless	PTFE	25mm	5	20ml	1500mm
675 1220B300	316L stainless	316L stainless	25mm	3	10ml	300mm
675 1220B600	316L stainless	316L stainless	25mm	3	15ml	600mm
675 1220B900	316L stainless	316L stainless	25mm	3	20ml	900mm
675 1220B1500	316L stainless	316L stainless	25mm	5	20ml	1500mm
675 1220J900	316L stainless	316L stainless	40mm	3	90ml	900mm
675 1220J1500	316L stainless	316L stainless	40mm	4	90ml	1500mm
675 1220J2000	316L stainless	316L stainless	40mm	4	90ml	2000mm

Stock No.	
675 8005A01	Sealing Sleeve Set - Covers pockets - set of 3 sleeves (25mm diameter - suitable for 1220A and 1220B)
675 8005A02	Sealing Sleeve Set - Covers pockets - set of 3 sleeves (40mm diameter - suitable for 1220J)
675 1220X600	Emptying rack for 600mm sampler (25mm diameter - suitable for 1220A and 1220B)
675 1220X900	Emptying rack for 900mm sampler (25mm diameter - suitable for 1220A and 1220B)
675 1220X1500	Emptying rack for 1500mm sampler (25mm diameter - suitable for 1220A and 1220B)
675 1220Y900	Emptying rack for 900mm sampler (40mm diameter - suitable for 1220J)
675 1220Y1500	Emptying rack for 1500mm sampler (40mm diameter - suitable for 1220J)
675 1220Y2000	Emptying rack for 2000mm sampler (40mm diameter - suitable for 1220J)
675 LUG1	Earthing connection point. See page 123 for more information
675 TIP2	Round tip. (Sampler supplied with pointed tip). For 25mm diameter samplers only - 1220A and 1220B
675 TIP3	Round tip. (Sampler supplied with pointed tip). For 40mm diameter samplers only - 1220J
Cleaning brushes	See page 129 for full range
Storage Cases	See page 130 for full range
XRF	Material certification verified by XRF (see page 139)

World Class Equipment
worldwide