

Sack Master

The World's Best Range of High Quality Sack Samplers

The Sack Master range has been specially designed to take samples through the side of a sack.

A unique range of sample collection methods are available.

- Single point
- 316 stainless steel or HDPE

Operation

1. Insert the sampler through the side of the sack.
2. Angle sampler downwards to allow the product to flow into the sample collecting container
3. Seal the hole using an ultra adhesive Sack Patch (see opposite page)



A) PLAIN END


- Sample collecting bag is held over end of sampler
- Plain end

B) END CAP

- Cap screws on to end of Sack Sampler
- Easily removed for cleaning
- Sample is retained in Sack Sampler

C) Bottle Adapter

- Adapter screws on to end of Sack Sampler
- Sample is collected in either a 250ml or 500ml bottle
- After sampling unscrew bottle and screw on the plastic bottle cap



QUOTE REQUEST ✓

BUY ONLINE ✓

Stock No.	Description	Material	Length	Diameter	End Fitting
675 1320A01	Sack Master P	316ss	400mm	25mm	Plain
675 1320B01	Sack Master EC	316ss	420mm	25mm	End Cap
675 1320C01	Sack Master BA	316ss	420mm	25mm	Bottle Adapter*
* Sampler supplied with one 250ml Sample Bottle (Part no. 675 8165A250)					
675 8165A250	Sampling bottle - HDPE. 250ml for use with bottle adapter				
675 8165A500	Sampling bottle - HDPE. 500ml for use with bottle adapter				
675 8020A600	Cleaning brush - 600mm length				

